



TRANSFER ANDENTREPRENEUR CENTRE

Drag grinding system

Edges, tools and other components can be rounded or deburred with the drag grinding system.

Training period for independent usage, without any pre knowledge: approx. 4 h

Otec DF-3 HD for wet and dry processing

With the drag grinding system, various surfaces and edges can be precisely finished.

Surface grades smaller than Ra 0.1 can be easily achieved with the system and multistage processing with various abrasives.



| | |
|----------------------------|----------------------------------|
| Container volume | 80 l |
| Maximum immersion depth | 250 mm |
| Maximum workpiece diameter | 210 mm |
| Editing media | Ceramics, plastic, corn granules |