



TRANSFER AND ENTREPRENEUR CENTRE

Drag grinding system

Edges, tools and other components can be rounded or deburred with the drag grinding system.

Training period for independent usage, without any pre knowledge: approx. 4 h

Otec DF-3 HD for wet and dry processing

With the drag grinding system, various surfaces and edges can be precisely finished.

Surface grades smaller than Ra 0.1 can be easily achieved with the system and multistage processing with various abrasives.



Container volume	80 l
Maximum immersion depth	250 mm
Maximum workpiece diameter	210 mm
Editing media	Ceramics, plastic, corn granules